Hydrotite - Hydrophilic Water Swelling Material -

Features




Hydrotite is well known as a superior water sealant.

Unlike conventional water sealants, Hydrotite has a unique double action system. First, the rubber elasticity forms a seal between the two surfaces. Second, unique to Hydrotite, the rubber absorbs water thus expanding within the joint gap, increasing sealing pressure water leakage is prevented as any joint opening due to external forces is automatically sealed by Hydrotite's water absorption.

Hydrotite products are world renowned for their long term stability and durability. Hydrotite seals can vary in their expandability depending on the required design and specific application.







Hydrotite continues to be used in a variety of applications from under water tunnels and water supply/drainage systems to civil engineering construction projects. Hydrotite prevents leakage problems before they occur.












■Products

Varied Product Range provides a Wide Variety of Applications

Hydrotite is suitable for a variety of applications. Hydrotite has an extensive product range applicable to many operating conditions and meeting a wide range of requirements.





For Segment Lining Tunnels

Hydrotite SS, RS, DS series

-Various shapes, compositions and properties.

For Concrete Construction Joints

Hydrotite CJ series

- Composite sealing material with holes.



For Concrete Pipe Joints Hydrotite BH, JH series

- Composite sealing material.



For In-situ Concrete Joints
LEAKMASTER

- Water Swelling Sealant



For Regular shaped joints

Hydrotite O-ring and washer

- Molded Seal and Packing

Typical Profiles

For Segment Lined Tunneling



SS Type RSType

<u>~~</u> ~

DS Type

Concrete Joints

CJ Type

For Poured

For Concrete Pipe Joints

ВН Туре

For Leak Repairing

RSS Type



For Segment Lining Tunnels

<Super-Low expansion type>


■Properties

Test item	unit	Hydrophilic Rubber	Non-hydrophilic Rubber	Standard
Hardness	-	A40±5	A45±5	JIS K 6253
Tensile strength	MPa	min. 3.9	min. 3.9	JIS K 6251
Elongation	%	min. 600	min. 500	JIS K 6251
Expansion rate	%	min. 100	-	in-house test*

^{*:} Expansion condition is at 23C in distilled water for 28 days

Note: Specimen: Pressed rubber sheet made of the same compound of the products

Note: The specifications shown above may be changed without notice to improve product quality.



Test water: Distilled water Water temp.: 23C Expansion type: Free expansion

Specimen: Pressed rubber sheet made of the same compound of products

Note: The data is only measured value, not guaranteed value.



■Main Items

	Shape	Item Code	Dimensions	Packing unit
			(txW1xW2)	(M x rolls/carton)
Composite structure	W2 W1	DTRO-03515-10 DTRO-0415-10 DTRO-0518-12	3.5×15×10 4×15×10 5×18×12	20×5 20×5 20×5
Composite structure	$\begin{array}{c c} & & & \\ \hline & & \\ \hline & & & \\ \hline & \\ \hline & & \\ \hline & \\$	DSHO-03514-13 DSHO-0418-14 DSHO-0518-16 DSHO-05520-15	3.5×14×13 4×18×14 5×18×16 5.5×20×15	20×5 20×5 20×5 20×5
Single structure	W2 W1	DTRO-03515-10 DTRO-0415-10 DTRO-0518-12	3.5×15×10 4×15×10 5×18×12	20×5 20×5 20×5



<Low expansion type>


■Properties

Test item	unit	Hydrophilic Rubber	Chloroprene Rubber	Standard
Hardness	-	A50±5	A50±5	JIS K 6253
Tensile strength	MPa	min. 3.9	min.8.8	JIS K 6251
Elongation	%	min. 600	min. 400	JIS K 6251
Expansion rate	%	min. 200	-	in-house test*

^{*:} Expansion condition is at 23C in distilled water for 28 days

Note: Specimen: Pressed rubber sheet made of the same compound of the products

Note: The specifications shown above may be changed without notice to improve product quality.



Test water: Distilled water

Water temp.: 23C

Expansion type: Free expansion

Specimen: Pressed rubber sheet made of the same compound of products.

Note: The data is only measured value, not guaranteed value.

■Main Items

	Shape	Item Code	Dimensions (txW1xW2)	Packing unit (M x rolls /carton)
Composite structure	$\begin{array}{c c} & & & \\ \hline \end{array}$	DST-0420-25-I DST-0520-35-I	4×2.5×20 5×3.5×20	20×5 20×5
Composite structure	w t	RST-0320-20-I RST-0520-35-I RST-0515-35-I RST-05515-40-I	3×2×20 5×3.5×20 5×3.5×15 5.5×4×15	20×5 20×5 20×5 20×5
Single structure	$\begin{array}{c c} & & & \downarrow \\ & & & \downarrow \\ & & & & \downarrow \\ & & & &$	SST-0215 SST-0218 SST-0220	2×15 2×18 2×20	25×4 25×4 25×4

Hydrophilic rubber



■Durability

■Ongoing long term water sealing test

As of Dec/2005 the tests are ongoing.

No.	Dimensions (thick x width mm)	Gap of both flanges (mm)	Year. Month '82.1 '83.1 '84.1 '85.1 '86.1 '87.1~'03.1 '04.1 '05.1 '05.12
1	3X20	2	<u> </u>
2	5X20	4	
3	5X20	5	

^{*}water pressure: 0.15MPa

Warranty

All statements regarding this product are based upon procedures and tests which we believe are reliable, and may be changed for improvement of quality without any notice; but it will be the sole responsibility of the customer and/or end user to use this product properly, and therefore assume all risk and liability in connection therewith.

C. I. Kasei Co., Ltd. Warrants its products to be of good quality and will replace product proved to be defective. In no instance will C. I. Kasei Co., Ltd. be liable for labor costs or incidental damage associated with the use of this product, unless stated in a warranty for a specific project.

^{*}No.1-2: Specimen is stuck on bottom flange that has no groove.

^{*}No.3: Specimen is stuck on both flanges that have grooves (2mm depth